

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash 3000

Formerly - PowerClean® 1 or 2 Wire Braid



Pressure Wash 3000

Color	Hose I.D.	Hose O.D.	Max. W.P.	Vac.	MBR	Wt. Per ft	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ft			
	(in)												(mm)	(psi)	(Bar)
Black	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	300	Reel	S	Stock	4657-2402	\$3.60
Black	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	1000	Reel	S	Stock	4657-2401	3.47
Black	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	300	Reel	S	Stock	4657-9375	4.13
Black	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.24	1000	Reel	S	Stock	4657-9376	3.98
Black	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.24	2800	Bale	S	Stock	4657-9530	3.98
Blue	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	300	Reel	S	Stock	4657-2404	3.78
Blue	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	1000	Reel	S	Stock	4657-2403	3.65
Blue	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	300	Reel	S	Stock	4657-9456	4.34
Blue	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	1000	Reel	S	Stock	4657-9455	4.18
Blue	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	2800	Bale	S	Stock	4657-9531	4.18
Gray	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	300	Reel	S	Stock	4657-2416	3.78
Gray	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	300	Reel	S	Stock	4657-9458	4.34
Gray	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	1000	Reel	S	Stock	4657-9457	4.18
Gray	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	2800	Bale	S	Stock	4657-9532	4.18
Yellow	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.23	300	Reel	S	Stock	4657-2417	3.78
Yellow	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.24	1000	Reel	S	MTO	4657-2652	3.65
Yellow	3/8	9.5	.67	17.0	3000	210	30.0	2.5	.24	3800	Bale	S	MTO	4657-0238	3.65
Yellow	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	300	Reel	S	Stock	4657-9460	4.34
Yellow	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	1000	Reel	S	Stock	4657-9459	4.18
Yellow	1/2	12.7	.79	20.0	3000	210	30.0	3.5	.25	2800	Bale	S	Stock	4657-9533	4.18

Pressure Wash 3000 - Cut Lengths

Color	Hose I.D.	Hose O.D.	Max. W.P.	Vac.	MBR	Wt. Per ea	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ea			
	(in)												(mm)	(psi)	(Bar)
Black	3/8	9.5	.67	17.0	3000	210	30.0	2.5	11.83	50	Ctn	T	MTO	4657-2469	\$203.27
Yellow	3/8	9.5	.67	17.0	3000	210	30.0	2.5	12.22	50	Ctn	T	Stock	4657-0064	138.28

RECOMMENDED FOR: Hot and cold water high-pressure cleaning equipment used in commercial and industrial cleaning, food processing, sanitation, and car wash applications where heavy-duty service is required. Specially compounded cover to handle harsh environments.

CAUTION: Not recommended for steam service. Use bend restrictors to extend service life.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Meets 300°F (150°C) intermittent per EN1829-2. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION:
Tube: Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Non-marking except for black. Abrasion-resistant, Ozone-resistant, MSHA-flame resistant.

COUPLINGS: 74 Gates MegaCrimp® and Pro™ Series couplings. Reference the Hose Coupling Section.

STANDARDS: Meets MSHA Flame-resistant. Exceeds EN1829-2.

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash 4000

Formerly - PowerClean® 1 or 2 Wire Braid



Color	Hose I.D.		Hose O.D.		Max. W.P.		Vac.	MBR	Wt. Per ft	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ft
	(in)	(mm)	(in)	(mm)	(psi)	(Bar)	(In. Hg)	(in)	(Lbs.)	(ft)			(ft)		
Black	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.15	300	Reel	S	Stock	4657-9377	\$3.15
Black	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.13	1000	Reel	S	Stock	4657-9378	3.20
Black	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.13	5600	Bale	S	Stock	4657-9534	3.20
Black	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	300	Reel	S	Stock	4657-9379	4.34
Black	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	1000	Reel	S	Stock	4657-9380	4.17
Black	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	3800	Bale	S	Stock	4657-9535	4.17
Black	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	300	Reel	S	Stock	4657-9462	4.98
Black	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	1000	Reel	S	Stock	4657-9351	4.80
Black	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	2250	Bale	S	Stock	4657-9536	4.80
Blue	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.15	300	Reel	S	Stock	4657-9474	3.49
Blue	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.15	1000	Reel	S	Stock	4657-9473	3.36
Blue	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	300	Reel	S	Stock	4657-9468	4.55
Blue	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.22	1000	Reel	S	Stock	4657-9467	4.38
Blue	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.20	3800	Bale	S	Stock	4657-9537	4.38
Blue	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	2250	Bale	S	Stock	4657-9538	5.05
Gray	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.14	300	Reel	S	Stock	4657-9476	3.49
Gray	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.14	1000	Reel	S	Stock	4657-9475	3.36
Gray	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.14	5600	Bale	S	Stock	4657-9539	3.36
Gray	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	300	Reel	S	Stock	4657-9472	4.55
Gray	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.19	1000	Reel	S	Stock	4657-9471	4.38
Gray	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.20	3800	Bale	S	Stock	4657-9540	4.38
Gray	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	300	Reel	S	Stock	4657-9464	5.24
Gray	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	2250	Bale	S	Stock	4657-9541	5.05
Yellow	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.15	300	Reel	S	Stock	4657-9478	3.49
Yellow	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.14	1000	Reel	S	Stock	4657-9477	3.36
Yellow	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.18	300	Reel	S	Stock	4657-9395	4.55
Yellow	3/8	9.5	.67	17.0	4000	280	30.0	2.5	.20	1000	Reel	S	Stock	4657-9396	4.38
Yellow	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	300	Reel	S	Stock	4657-9466	5.24
Yellow	1/2	12.7	.80	20.3	4000	280	30.0	3.5	.28	1000	Reel	S	Stock	4657-9465	5.05

RECOMMENDED FOR: Hot and cold water high-pressure cleaning equipment used in commercial and industrial cleaning, food processing, sanitation, and car wash applications where heavy-duty service is required. Specially compounded cover to handle harsh environments.

CAUTION: Not recommended for steam service. Use bend restrictors to extend service life.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Meets 300°F (150°C) intermittent per EN1829-2. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION: **Tube:** Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Non-marking except for black. Abrasion-resistant, Ozone-resistant, MSHA-flame resistant.

COUPLINGS: 74 Gates MegaCrimp® and Pro™ Series couplings. Reference the Hose Coupling Section.

STANDARDS: Meets MSHA Flame-resistant. Exceeds EN1829-2.

AGRICULTURE

AIR BREATHING

AIR DUCT

AIR AND MULTI-PURPOSE

CHEMICAL

FOOD AND BEVERAGE

MARINE AND ENGINE

MATERIAL HANDLING

MINING

OILFIELD

PETROLEUM

PRESSURE WASH AND WASHDOWN

STEAM

WATER

CLAMPS

COUPLINGS AND FERRULES

HOSE FINDER

CHEMICAL RESISTANCE TABLE

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash 4000 - Cut Lengths



Color	Hose I.D.		Hose O.D.		Max. W.P.		Vac.	MBR	Wt. Per ea	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ea
	(in)		(mm)		(in)										
Black	3/8	9.5	.67	17.0	4000	280	30.0	2.5	10.24	50	Ctn	T	Stock	4657-9424	\$223.30
Black	3/8	9.5	.67	17.0	4000	280	30.0	2.5	31.47	100	Ctn	T	Stock	4657-9423	432.95
Blue	1/4	6.4	.53	13.5	4000	280	30.0	2.0	.14	100	Ctn	T	MTO	4657-9586	523.58
Blue	3/8	9.5	.67	17.0	4000	280	30.0	2.5	10.24	50	Ctn	T	Stock	4657-9469	334.09
Blue	3/8	9.5	.67	17.0	4000	280	30.0	2.5	31.47	100	Ctn	T	Stock	4657-9470	558.81

RECOMMENDED FOR: Hot and cold water high-pressure cleaning equipment used in commercial and industrial cleaning, food processing, sanitation, and car wash applications where heavy-duty service is required. Specially compounded cover to handle harsh environments.

CAUTION: Not recommended for steam service. Use bend restrictors to extend service life.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Meets 300°F (150°C) intermittent per EN1829-2. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION:
Tube: Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Non-marking except for black. Abrasion-resistant, Ozone-resistant, MSHA-flame resistant.

COUPLINGS: 74 Gates MegaCrimp® and Pro™ Series couplings. Reference the Hose Coupling Section.

STANDARDS: Meets MSHA Flame-resistant. Exceeds EN1829-2.

AGRICULTURE
AIR BREATHING
AIR DUCT
AIR AND MULTI-PURPOSE
CHEMICAL
FOOD AND BEVERAGE
MARINE AND ENGINE
MATERIAL HANDLING
MINING
OILFIELD
PETROLEUM
PRESSURE WASH AND WASHDOWN
STEAM
WATER
CLAMPS
COUPLINGS AND FERRULES
HOSE FINDER
CHEMICAL RESISTANCE TABLE

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash 5000

Formerly - PowerClean® 1 or 2 Wire Braid



Pressure Wash 5000

Color	Hose I.D.		Hose O.D.		Max. W.P.		Vac.	MBR	Wt. Per ft	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ft
	(in)		(mm)		(in)										
Black	3/8	9.5	.64	16.3	5000	350	30.0	2.5	.35	300	Reel	S	Stock	4657-2407	\$5.07
Black	3/8	9.5	.64	16.3	5000	350	30.0	2.5	.35	1000	Reel	S	Stock	4657-2406	4.88
Black	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.39	300	Reel	S	Stock	4657-9387	5.35
Black	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.39	1000	Reel	S	Stock	4657-9388	5.15
Black	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	2250	Bale	S	Stock	4657-9542	5.15
Blue	3/8	9.5	.64	16.3	5000	350	30.0	2.5	.35	300	Reel	S	Stock	4657-2429	5.33
Blue	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	300	Reel	S	Stock	4657-9480	6.03
Blue	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	1000	Reel	S	Stock	4657-9479	5.81
Blue	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	2250	Bale	S	Stock	4657-9543	5.81
Gray	3/8	9.5	.64	16.3	5000	350	30.0	2.5	.35	300	Reel	S	MTO	4657-2430	5.33
Gray	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	300	Reel	S	MTO	4657-9482	6.03
Gray	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	1000	Reel	S	MTO	4657-9481	5.81
Yellow	3/8	9.5	.64	16.3	5000	350	30.0	2.5	.35	300	Reel	S	Stock	4657-2431	5.33
Yellow	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	300	Reel	S	MTO	4657-9484	6.03
Yellow	1/2	12.7	.86	21.8	5000	350	30.0	3.5	.25	1000	Reel	S	MTO	4657-9483	5.81

Pressure Wash 5000 - Cut Lengths

Color	Hose I.D.		Hose O.D.		Max. W.P.		Vac.	MBR	Wt. Per ea	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ea
	(in)		(mm)		(in)										
Black	3/8	9.5	.64	16.3	5000	350	30.0	2.5	17.92	50	Ctn	T	Stock	4657-2472	\$419.33

RECOMMENDED FOR: Hot and cold water high-pressure cleaning equipment used in commercial and industrial cleaning, food processing, sanitation, and car wash applications where heavy-duty service is required. Specially compounded cover to handle harsh environments.

CAUTION: Not recommended for steam service. Use bend restrictors to extend service life.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Meets 300°F (150°C) intermittent per EN1829-2. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION:
Tube: Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Non-marking except for black. Abrasion-resistant, Ozone-resistant, MSHA-flame resistant.

COUPLINGS: 74 Gates MegaCrimp® and Pro™ Series couplings. Reference the Hose Coupling Section.

STANDARDS: Meets MSHA Flame-resistant. Exceeds EN1829-2.

AGRICULTURE

AIR BREATHING

AIR DUCT

AIR AND MULTI-PURPOSE

CHEMICAL

FOOD AND BEVERAGE

MARINE AND ENGINE

MATERIAL HANDLING

MINING

OILFIELD

PETROLEUM

PRESSURE WASH AND WASHDOWN

STEAM

WATER

CLAMPS

COUPLINGS AND FERRULES

HOSE FINDER

CHEMICAL RESISTANCE TABLE

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash 6000

Formerly - PowerClean® 1 or 2 Wire Braid



Pressure Wash 6000

Color	Hose I.D.		Hose O.D.		Max. W.P. (psi)	(Bar)	Vac. (In. Hg)	MBR (in)	Wt. Per ft (Lbs.)	Length (ft)	Std. Pack	Pkg Code	Stock or MTO (ft)	Gates Item No.	List Price Per ft
	(in)	(mm)	(in)	(mm)											
Black	1/4	6.4	.59	15.0	6000	420	30.0	2.0	.25	300	Reel	S	Stock	4657-2410	\$4.11
Black	1/4	6.4	.59	15.0	6000	420	30.0	2.0	.25	1000	Reel	S	Stock	4657-9485	3.96
Black	1/4	6.4	.59	15.0	6000	420	30.0	2.0	.22	4000	Bale	S	Stock	4657-9544	3.96
Black	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	300	Reel	S	Stock	4657-9385	5.78
Black	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.33	1000	Reel	S	Stock	4657-9386	5.57
Black	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.31	2400	Bale	S	Stock	4657-9545	5.57
Blue	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	300	Reel	S	Stock	4657-9487	6.00
Blue	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	1000	Reel	S	Stock	4657-9486	5.78
Blue	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	2400	Bale	S	Stock	4657-9546	5.78
Gray	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	300	Reel	S	Stock	4657-9491	6.00
Gray	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.31	1000	Reel	S	MTO	4657-9490	5.78
Gray	3/8	9.5	.64	16.3	6000	420	30.0	2.5	.32	2400	Bale	S	Stock	4657-9547	5.78

Pressure Wash 6000 - Cut Lengths

Color	Hose I.D.		Hose O.D.		Max. W.P. (psi)	(Bar)	Vac. (In. Hg)	MBR (in)	Wt. Per ea (Lbs.)	Length (ea)	Std. Pack	Pkg Code	Stock or MTO (ea)	Gates Item No.	List Price Per ea
	(in)	(mm)	(in)	(mm)											
Black	3/8	9.5	.64	16.3	6000	420	30.0	2.5	15.74	50	Ctn	T	Stock	4657-9422	\$259.67
Black	3/8	9.5	.64	16.3	6000	420	30.0	2.5	32.30	100	Ctn	T	Stock	4657-9421	510.81
Blue	3/8	9.5	.64	16.3	6000	420	30.0	2.5	15.74	50	Ctn	T	Stock	4657-9488	374.63
Blue	3/8	9.5	.64	16.3	6000	420	30.0	2.5	32.30	100	Ctn	T	Stock	4657-9489	734.60

RECOMMENDED FOR: Hot and cold water high-pressure cleaning equipment used in commercial and industrial cleaning, food processing, sanitation, and car wash applications where heavy-duty service is required. Specially compounded cover to handle harsh environments.

CAUTION: Not recommended for steam service. Use bend restrictors to extend service life.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Meets 300°F (150°C) intermittent per EN1829-2. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION:
Tube: Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Non-marking except for black. Abrasion-resistant, Ozone-resistant, MSHA-flame resistant.

COUPLINGS: 74 Gates MegaCrimp® and Pro™ Series couplings. Reference the Hose Coupling Section.

STANDARDS: Meets MSHA Flame-resistant. Exceeds EN1829-2.

Pressure Wash and Washdown Hose

Clean Master® Pressure Wash Assemblies



Color	Hose I.D.		Hose O.D.		Max. W.P.		Vac.	MBR	Wt. Per ea	Length	Std. Pack	Pkg Code	Stock or MTO	Gates Item No.	List Price Per ea
	(in)	(mm)	(in)	(mm)	(psi)	(Bar)	(In. Hg)	(in)	(Lbs.)	(ea)			(ea)		
Black	3/8	9.5	.63	16.0	3000	210	30.0	2.5	9.60	50	Assy	5	Stock	3604-0035	\$191.73
Black	3/8	9.5	.63	16.0	3000	210	30.0	2.5	19.40	100	Assy	5	Stock	3604-0071	291.98
Black	1/2	12.7	.76	19.3	3000	210	30.0	3.5	12.98	50	Assy	5	Stock	3604-0036	222.18

RECOMMENDED FOR: Standard-duty use on hot and cold water high-pressure cleaning equipment. Extremely flexible, lightweight and easy to handle. Tube specially compounded to handle high-pressure water service. Specially compounded cover to handle pressure washer environment.

CAUTION: Not recommended for steam service.

TEMPERATURE: -40°F to +250°F (-40°C to +121°C). Laboratory tested for normal service. Increased operating temperatures will reduce hose assembly service life.

CONSTRUCTION:
Tube: Type C (Nitrile). Black.
Reinforcement: Braided, high tensile steel wire.
Cover: Type C2 (Modified Nitrile). Black.

COUPLINGS: Gates permanent couplings (MP/MPX with bend restrictors applied on each end). Factory coupled assemblies only.

STANDARDS: Exceeds EN1829-2.

AGRICULTURE

AIR BREATHING

AIR DUCT

AIR AND MULTI-PURPOSE

CHEMICAL

FOOD AND BEVERAGE

MARINE AND ENGINE

MATERIAL HANDLING

MINING

OILFIELD

PETROLEUM

PRESSURE WASH AND WASHDOWN

STEAM

WATER

CLAMPS

COUPLINGS AND FERRULES

HOSE FINDER

CHEMICAL RESISTANCE TABLE