

















MXT-XTP™

| | -8 MXT-XTP | -8 SAE100R16 | -8 SAE 100R2 AT |
|---|-------------------|---------------------|------------------------|
|  WP | 4000 PSI | 3989 PSI | 3989 PSI |
|  Weight (LBS) | 0.31 | 0.39 | 0.43 |
|  OD (IN) | 0.795 | 0.866 | 0.909 |
|  MBR (IN) | 2.8 | 3.54 | 7.09 |
|  Temp (F) | -40 to +212 | -40 to +212 | -40 to +212 |
|  Ozone | Best | Good | Good |
|  Abrasion | 25X Better | Not Specified | Not Specified |

**MXT™**

| | -8 MXT | -8 SAE100R16 | -8 SAE 100R2 AT |
|---|---------------|---------------------|------------------------|
|  WP | 4000 PSI | 3989 PSI | 3989 PSI |
|  Weight (LBS) | 0.31 | 0.39 | 0.43 |
|  OD (IN) | 0.795 | 0.866 | 0.909 |
|  MBR (IN) | 2.8 | 3.54 | 7.09 |
|  Temp (F) | -40 to +212 | -40 to +212 | -40 to +212 |
|  Ozone | Better | Good | Good |
|  Abrasion | Good | Not Specified | Not Specified |