

# POWERATED™

## GREEN TEXTILE WRAPPED V-BELT WITH ARAMID CORD

Designed as an alternative to conventional light-duty belts, with high-performance construction to deliver more horsepower, less stretch, and provide longer service life.

### CONSTRUCTION + SPECIFICATIONS

- **Bareback construction** for smooth clutching on shock loaded, backside-idler driven equipment.
- **Aramid tensile cords** combine limited stretch with extraordinary strength and durability.

#### BELT IDENTIFICATION

Singles: **6726 / 3L260K**  
**67 / 3L** - Cross Section  
**26 / 260** - Outside Circumference (in) / Outside Circumference (in), plus added zero to designate part number  
**K** - Aramid Designation

#### Available Stock Sizes

**67/3L** 16-74 (in)  
**68/4L** 17-117 (in)  
**69/5L** 23-100 (in)

### FEATURES + BENEFITS

- Suitable for outdoor power equipment, appliances, and industrial applications where Fractional Horsepower (FHP) belts are typically used.
- Low cord positioning in thin profile gives extreme flexibility.
- Meets ARPM/RMA IP-3-2 oil and heat resistant standards.
- REACH and RoHS 2 compliant.
- Operating temperature range: -30°C/-22°F to +60°C/140°F.

#### Belt Identification Chart

